

Hostaform® C 13021 10/1570

聚甲醛 (POM) 共聚物
Celanese Corporation

产品说明

POM copolymer
Easy flowing Injection molding type for precision molded parts and thin-walled molded parts with high rigidity, hardness and toughness; good chemical resistance to solvents, fuel and strong alkalis as well as good hydrolysis resistance; high resistance to thermal and oxidative degradation. With a high amount of carbon black
.
Ranges of applications: automotive engineering, especially out door applications

供应商联系方式

上海松翰塑化科技有限公司

电话: 13061808058

联系人: 赵先生

邮箱: sales@su-jiao.com

基本信息

添加剂	碳黑		
特性	刚性,高	抗溶剂性	良好的流动性
	耐化学性良好	耐碱	耐燃油性
	耐水解性	韧性良好	硬度高
用途	薄壁部件	汽车领域的应用	汽车外部零件
RoHS 合规性	联系制造商		
加工方法	注射成型		
物理性能	额定值	单位制	测试方法
密度	1.41	g/cm³	ISO 1183
溶化体积流率(MVR) (190°C/2.16 kg)	12.0	cm³/10min	ISO 1133
收缩率			ISO 294-4
横向流量	1.8	%	ISO 294-4
流量	2.0	%	ISO 294-4
吸水率 (饱和, 23°C)	0.65	%	ISO 62
机械性能	额定值	单位制	测试方法
拉伸模量	2900	MPa	ISO 527-2/1A/1
拉伸应力 (屈服)	65.0	MPa	ISO 527-2/1A/50
拉伸应变 (屈服)	9.0	%	ISO 527-2/1A/50
标称拉伸断裂应变	25	%	ISO 527-2/1A/50
拉伸蠕变模量			ISO 899-1
1 hr	2500	MPa	ISO 899-1
1000 hr	1300	MPa	ISO 899-1
弯曲模量 (23°C)	2800	MPa	ISO 178
冲击性能	额定值	单位制	测试方法
简支梁缺口冲击强度			ISO 179/1eA
-30°C	6.0	kJ/m²	ISO 179/1eA
23°C	6.5	kJ/m²	ISO 179/1eA
简支梁无缺口冲击强度			ISO 179/1eU

-30℃	140	kJ/m²	ISO 179/1eU
23℃	150	kJ/m²	ISO 179/1eU
热性能	额定值	单位制	测试方法
热变形温度 (1.8 MPa, 未退火)	106	℃	ISO 75-2/A
熔融温度 ¹	166	℃	ISO 11357-3
线形热膨胀系数 - 流动	1.1E-4	cm/cm/℃	ISO 11359-2
电气性能	额定值	单位制	测试方法
表面电阻率	1.0E+14	ohms	IEC 60093
体积电阻率	1.0E+14	ohms-cm	IEC 60093
介电强度	35	kV/mm	IEC 60243-1
相对电容率			IEC 60250
100 Hz	4.00		IEC 60250
1 MHz	4.00		IEC 60250
耗散因数			IEC 60250
100 Hz	2.0E-3		IEC 60250
1 MHz	5.0E-3		IEC 60250
漏电起痕指数	600	V	IEC 60112
充模分析	额定值	单位制	测试方法
Density of Melt	1.200	g/cm³	内部方法
Specific Heat Capacity of Melt	2210	J/kg/℃	内部方法
Thermal Conductivity of Melt	0.16	W/m/K	内部方法
Ejection Temperature	140	℃	内部方法
注射	额定值	单位制	测试方法
干燥温度	120 到 140	℃	
干燥时间	3.0 到 4.0	hr	
建议的最大水分含量	0.15	%	
料斗温度	20 到 30	℃	
料筒后部温度	170 到 180	℃	
料筒中部温度	180 到 190	℃	
料筒前部温度	190 到 200	℃	
射嘴温度	190 到 210	℃	
加工(熔体)温度	190 到 210	℃	
模具温度	80 到 120	℃	
注塑压力	60.0 到 120	MPa	
注射速度	慢到中等		
保压	60.0 到 120	MPa	
背压	0.00 到 4.00	MPa	
注射说明	Manifold Temperature: 190 to 210℃Zone 4 Temperature: 190 to 210℃Feed Temperature: 60 to 80℃		
备注			
1.	10℃/min		